



Main

Range of product	NSX100...250 Easypact CVS100...250
Range	Compact
Product or component type	Vigi add-on
Device application	Wiring
Range compatibility	Easypact - EasyPact CVS circuit breaker Compact - Compact NSX circuit breaker
Poles description	3P
[In] rated current	100 A 160 A
Earth-leakage add-on module name	MH
Earth-leakage protection class	Class A
Residual earth-leakage sensitivity adjustment type	Adjustable 5 settings
[I Δ n] residual earth-leakage sensitive adjustment	0.03...10 A
Residual earth-leakage time delay adjustment type	Adjustable 5 settings
[Δ t] residual earth-leakage time delay adjustment	0 ms 150 ms 310 ms 60 ms

Complementary

Network type	AC
Network frequency	50/60 Hz
[U _e] rated operational voltage	200...440 V AC 50/60 Hz conforming to IEC 60947-2
Earth-leakage protection	With
Maximum breaking time	< 800 ms
Overvoltage category	Class II

Environment

Electrical shock protection class	Class II
Standards	IEC 60947-2

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0818 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile

Contractual warranty

Warranty period	18 months
-----------------	-----------
