



Main

Device short name	MX
Product or component type	Voltage release
Device application	Control
Range compatibility	Compact NSX PowerPact Multistandard
Voltage release type	Shunt trip release
[Uc] control circuit voltage	600 V AC 60 Hz 525 V AC 50 Hz

Complementary

Control signal type	Maintained Impulse
Impulse duration	≥ 20 ms
Threshold tripping voltage	$0.7 \dots 1.1 \times U_n$ opening
Supply inrush power	10 VA
Mounting mode	Fixed
Response time	50 ms
Auxiliary connection terminal	Screw terminal $0 \dots 1.5 \text{ mm}^2$

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Under investigation
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------
