



## Main

Range of product	NSX100...250
Range	Compact
Product or component type	Insulation monitoring device
Device application	Insulation
Range compatibility	Compact NSX circuit breaker
Poles description	3P
Network type	AC

## Complementary

[Ue] rated operational voltage	200...440 V
Network frequency	50/60 Hz
Residual earth-leakage sensitivity adjustment type	Adjustable
[Δn] residual earth-leakage sensitive adjustment	0.5 A 0.2 A 1 A 0.1 A
[Δt] residual earth-leakage time delay adjustment	5...10 s
Measurement accuracy	-50 %...0 %

## Environment

IP degree of protection	IP40 conforming to IEC 60529
IK degree of protection	IK04 conforming to IEC 62262

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>

### Contractual warranty

---

Warranty	18 months
----------	-----------

---