


Product data sheet

Specifications



trip unit TM200D for ComPact NSX 250 circuit breakers, thermal magnetic, rating 200 A, 3 poles 3d

LV431431

⚠ Discontinued on: Oct 26, 2023

⚠ Discontinued

Important message: This product has been switched to new ComPacT range and is no longer commercialized. It will continue to be available in H1 2023 only limited to specific projects.

Main

Range	ComPact
Range Of Product	ComPact NSX100...250
Product Or Component Type	Trip unit
Trip Unit Name	TM-D
Trip Unit Technology	Thermal-magnetic
Range Compatibility	ComPact NSX250
Device Application	Distribution
Number Of Poles	3P
Protected Poles Description	3t
Trip Unit Protection Functions	LI
Protection Type	L : for overload protection (thermal) I : for short-circuit protection (magnetic)
Trip Unit Rated Current	200 A at 40 °C
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz
Network Type	AC
Network Frequency	50/60 Hz

Complementary

Long-Time Pick-Up Adjustment Type Ir (Thermal Protection)	Adjustable
[Ir] Long-Time Protection Pick-Up Adjustment Range	0.7...1 x In
Long-Time Protection Delay Adjustment Type Tr	Fixed
[Tr] Long-Time Protection Delay Adjustment Range	120...400 s at 1.5 x In 15 s at 6 x Ir
Short-Time Protection Pick-Up Adjustment Type Isd	Adjustable
[Isd] Short-Time Protection Pick-Up Adjustment Range	5...10 x In
Short-Time Protection Delay Adjustment Type Tsd	Fixed
Earth-Leakage Protection	Without

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	UL 508 EN/IEC 60947-2
Product Certifications	EAC CCC Marine
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-50...85 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.500 cm
Package 1 Width	9.500 cm
Package 1 Length	11.500 cm
Package 1 Weight	463.200 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	28
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	13.382 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	224
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	119.054 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov