



Main

Device short name	Motor mechanism module with SDE adaptor
Product or component type	Motor mechanism
Device application	Automatic spring charging
Range compatibility	Compact - Compact NSX Compact - Compact NSX DC PowerPact Multistandard
Product compatibility	PowerPact H-Frame PowerPact J-Frame
[In] rated current	250 A
[Uc] control circuit voltage	250 V DC

Complementary

Control type	Standard
Control signal type	Maintained Impulse
Mounting mode	Fixed
Response time	< 600 ms - during opening time < 80 ms - during closing time
Maximum operating frequency	4 per minute
Power consumption in VA	<= 500 VA - during closing time <= 500 VA - during opening time
Provided equipment	SDE adaptor
Locking options description	1 to 3 padlocks Ø 5 to Ø 8 Padlocking in OFF position

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0909 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available

Contractual warranty

Warranty period	18 months
-----------------	-----------