



### Main

Range of product	INF100...160 INF63 INF200...800 INF40 INF32
Range	Fupact
Product or component type	Neutral link
Accessory / separate part category	Connection accessory
Range compatibility	Fupact INFD INFD40 Fupact INFD INFD63 Fupact INF INFB63 Fupact INF INFB100 Fupact INF INFC125 Fupact INFD INFD160 Fupact INF INFB160 Fupact INF INFC32 fuse-switch disconnecter Fupact INF INFB32 Fupact INF INFC63 Fupact INFD INFD200 Fupact INF INFB200 Fupact INFD INFD250 Fupact INF INFB250 Fupact INFD INFD400 Fupact INF INFB400 Fupact INFD INFD630 Fupact INF INFB630 Fupact INFD INFD800 Fupact INF INFB800

### Complementary

Mounting mode	External mounting
Connections - terminals	Screw 2.5...35 mm <sup>2</sup>
Tightening torque	1.9 N.m

### Offer Sustainability

RECh Regulation	<a href="#">REACH Declaration</a>
RECh free of SVHC	Yes
EU RoHS Directive	Compliant

### EU RoHS Declaration

Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)

### Contractual warranty

Warranty	18 months
----------	-----------