

Product data sheet

Characteristics

LV480885

Current transformer - class 1 - 150/5A - 2.5VA - for Fupact ISFL 250..630



Main

Range of product	ISFL1250 ISFL250...630
Range	Fupact
Product or component type	Current transformer
Device application	Power supply
Range compatibility	Fupact ISFL ISFL250 fuse-switch disconnecter Fupact ISFL ISFL400 Fupact ISFL ISFL630 Fupact ISFL ISFL1250
Current transformer ratio	150/5 A
Power consumption in VA	2.5 VA

Complementary

Accessory / separate part category	Measurement accessory
Current transformer type	Measurement class 1
Maximum safety factor	5
[U _e] rated operational voltage	800 V AC 50/60 Hz
IP degree of protection	IP20
Standards	VDE 0414 IEC 60044-1 BS 7626
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...80 °C
Height	78 mm
Width	60 mm
Depth	30 mm

Offer Sustainability

RECh Regulation	RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes

Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)

Contractual warranty

Warranty	18 months
----------	-----------