



### Main

Range of product	ISFL1250 ISFL250...630
Range	Fupact
Product or component type	Current transformer
Device application	Power supply
Range compatibility	Fupact ISFL ISFL250 fuse-switch disconnecter Fupact ISFL ISFL400 Fupact ISFL ISFL630 Fupact ISFL ISFL1250
Current transformer ratio	400/5 A
Power consumption in VA	5 VA

### Complementary

Accessory / separate part category	Measurement accessory
Current transformer type	Measurement class 1
Maximum safety factor	5
[Ue] rated operational voltage	800 V AC 50/60 Hz
IP degree of protection	IP20
Standards	IEC 60044-1 VDE 0414 BS 7626
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...80 °C
Height	78 mm
Width	60 mm
Depth	30 mm

### Offer Sustainability

RECh Regulation	<a href="#">RECh Declaration</a>
RECh free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes

Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)

### Contractual warranty

Warranty	18 months
----------	-----------