

# Product data sheet

Specifications



## Current transformer, FuPacT ISFL160, 1 pole, class 1, 150/5A, 5VA

LV480904

### Main

Range Of Product	ISFL160
Range	FuPacT
Product Or Component Type	Current transformer
Device Application	Power supply
Range Compatibility	FuPacT FuPacT ISFL ISFL160 fuse-switch disconnecter
Poles Description	1P
Current Transformer Ratio	150/5 A
Power Consumption In Va	5 VA

### Complementary

Accessory / Separate Part Category	Measurement accessory
Current Transformer Type	Measurement class 1
Maximum Safety Factor	5
[Ue] Rated Operational Voltage	800 V AC 50/60 Hz
Ip Degree Of Protection	IP20
Standards	VDE 0414 IEC 60044-1 BS 7626
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...80 °C

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.0 cm
Package 1 Width	5.0 cm
Package 1 Length	8.0 cm
Package 1 Weight	257.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	30
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Length	40.0 cm
Package 2 Weight	8.165 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations