



Main

Range	Masterpact
Device short name	MN diag
Product or component type	Voltage release
Device application	Safety
Range compatibility	Masterpact MTZ1 circuit breaker Masterpact MTZ2 circuit breaker Masterpact MTZ3 circuit breaker
Voltage release type	Undervoltage release

Complementary

Control type	Communicating
Signalling function	Error MN open Coil powered
[Uc] control circuit voltage	24 V AC 50/60 Hz 24...30 V DC
Threshold tripping voltage	0.35...0.7 Un opening 0.85 Un closing
Supply holding power	4.5 W
Mounting mode	Fixed
Response time	40 ms +/- 5 % for Masterpact MTZ1 90 ms +/- 5 % for Masterpact MTZ2 90 ms +/- 5 % for Masterpact MTZ3

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes

RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information