



## Main

Range	TeSys
Product or component type	Contactor coil
Device short name	LX4D7
Control circuit type	DC standard
[Uc] control circuit voltage	174 V DC
Average resistance	1394 Ohm at 20 °C
Product compatibility	LC1D80
Mechanical durability	10 Mcycles
Operating rate	3600 cyc/h at <= 60 °C

## Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	0.1...0.3 Uc at 55 °C drop-out 0.85...1.1 Uc at 55 °C operational
Time constant	75 ms
Inrush power in W	22 W at 20 °C
Hold-in power consumption in W	22 W at 20 °C

## Environment

Ambient air temperature for operation	-5...60 °C
Product weight	0.68 kg

## Contractual warranty

Warranty period	18 months
-----------------	-----------