



Main

Range	PowerLogic
Product name	CT
Product or component type	Current transformer
Secondary current	80 mA
[In] rated current	400 A

Complementary

Current transformer type	Standard for cable
Current transformer ratio	400 A/80 mA
[Ui] rated insulation voltage	600 V
Depth	11.2 mm
Diameter	25 mm inner: 47.1 mm outer:
Net weight	1.36 kg
[Uimp] rated impulse withstand voltage	10 kV

Environment

Product certifications	CE
------------------------	----

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins