



### Main

Range	Unica
Accessory / separate part category	Replacement accessories
Product or component type	Replacement LED
Aesthetic name	Unica
Light block colour	Blue
Bulb type	LED

### Complementary

[Ue] rated operational voltage	127/230 V AC switch
Current consumption	0.15 mA
Temperature rise	Max +15 °C above ambient temperature
Ambient air temperature for operation	-20...40 °C
Product weight	0.0027 kg

### Environment

Standards	UNE 60669-1
Environmental health and issues	Halogen free

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1834 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---