



### Main

Range of product	Unica
Aesthetic name	Unica (standard aesthetic)
Device application	Control
Product or component type	Switch
Device presentation	Complete mechanism
Switch function	2 x 1-pole 1-way
Number of rocker	2
Provided equipment	Internal power connection
Colour tint	Ivory

### Complementary

Rated current	10 AX, 250 V AC, 50/60 Hz
Electrical durability	10000 cycles
Insulation resistance	> 5 MOhm @500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi: 0.3
Opening distance	> 3 mm
Actuator	Rocker
Number of modules	2 modules
Connections - terminals	Screwless terminals
Cable cross section	0...2.5 mm <sup>2</sup> (rigid) 0...2.5 mm <sup>2</sup> (flexible)
Material	Cover frame : ASA + PC
Fixing mode	Long claws
Width	85 mm
Height	80 mm
Depth	34 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Embedding depth	22 mm
Product weight	0.025 kg
Ambient air temperature for operation	25...35 °C
Ambient air temperature for storage	0...50 °C
Standards	EMC directive EN 60669-1 LV directive

## Environment

IP degree of protection	IP20
IK degree of protection	IK01
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid
Environmental health and issues	Halogen free

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0622 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------