



### Main

Range	Unica
Device application	Mounting
Product or component type	Cover frame
Aesthetic name	Unica Basic
Number of gangs	3 gangs horizontal
Fixing mode	Clip-in
Cover frame colour tint	White
Decoration colour	White

### Complementary

Material	ASA + PC cover frame ASA + PC decorative frame ASA + PC intermediate part
Standards	EN 60669-1
Height	80 mm
Width	227 mm
Depth	14 mm
Distance between centers	71 mm
Product weight	0.042 kg
Market segment	Small commercial Residential

### Environment

IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Bleach Window-cleaning fluid UV resistant Ammonia

Liquid soap  
Acetone  
Petrol  
Alcohol  
Oil

---

Environmental health and issues	Halogen free
---------------------------------	--------------

---

### Offer Sustainability

---

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1834 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

---

### Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---