



Main

Range	Unica
Device application	Mounting
Product or component type	Cover frame
Aesthetic name	Unica Basic
Number of gangs	3 gangs horizontal
Fixing mode	Clip-in
Cover frame colour tint	Ivory
Decoration colour	Ivory

Complementary

Material	ASA + PC decorative frame ASA + PC intermediate part ABS (acrylonitrile butadiene-styrene) cover frame
Standards	EN 60669-1
Height	80 mm
Width	227 mm
Depth	14 mm
Distance between centers	71 mm
Product weight	0.042 kg

Environment

IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil

	Petrol UV resistant Window-cleaning fluid
Environmental health and issues	Halogen free

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1834 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------