



Main

| | |
|---------------------------|--------------------|
| Range | Unica |
| Device application | Mounting |
| Product or component type | Cover frame |
| Aesthetic name | Unica Basic |
| Number of gangs | 4 gangs horizontal |
| Fixing mode | Clip-in |
| Cover frame colour tint | Ivory |
| Decoration colour | Ivory |

Complementary

| | |
|--------------------------|---|
| Material | ASA + PC cover frame ASA + PC intermediate part Zamak cover frame |
| Standards | EN 60669-1 |
| Height | 80 mm |
| Width | 298 mm |
| Depth | 14 mm |
| Distance between centers | 71 mm |
| Product weight | 0.056 kg |
| Market segment | Residential Small commercial |

Environment

| | |
|------------------------------|---|
| IK degree of protection | IK01 |
| IP degree of protection | IP20 |
| Environmental characteristic | Acetone Alcohol Ammonia Bleach |

Liquid soap
Oil
Petrol
UV resistant
Window-cleaning fluid

| | |
|---------------------------------|--------------|
| Environmental health and issues | Halogen free |
|---------------------------------|--------------|

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 1834 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product environmental profile | Available Product Environmental Profile |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|
