



Main

Range	Unica
Device application	Mounting
Product or component type	Supplementary frame
Aesthetic name	Unica Basic Unica Colors
Number of modules	6 modules
Number of gangs	3 gangs
Fixing mode	Clip-in
Cover frame colour tint	White

Complementary

Material	ASA + PC
Standards	EN 60669-1
Depth	13.5 mm
Width	227 mm
Height	90 mm
Distance between centers	71 mm
Product weight	0.024 kg

Environment

IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid
Environmental health and issues	Halogen free

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0803 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------
