

Product data sheet

Specifications



Unica - 2 complete S.O. - 2P+E, DE - 2 m - ivory

MGU23.067.25D

 **Discontinued on:** Sep 30, 2023

 **Discontinued**

Main

| | |
|-------------------------------|----------------------------|
| Range | Unica |
| Product Or Component Type | Socket-outlet |
| Aesthetic Name | Unica (standard aesthetic) |
| Device Presentation | Complete mechanism |
| Device Mounting | Flush |
| Socket Number | 2 |
| Outlet Poles Configuration | 2P + E |
| Outlet Standard | Schuko |
| Outlet Standard Description | Side earth |
| Socket Additional Information | In pin pack |
| Rated Current | 16 A |

Complementary

| | |
|--------------------------------|----------------------------------------------------------------------------------------------------------------------------------------|
| Device Application | Power supply |
| [Ue] Rated Operational Voltage | 250 V |
| Network Type | AC |
| Network Frequency | 50/60 Hz |
| Number Of Modules | 2 modules |
| Fixing Mode | Long claws |
| Colour Tint | Cream (RAL 9010) |
| Connections - Terminals | Screw terminals |
| Cable Cross Section | 0...4 mm ² - cable stiffness: flexible 0...4 mm ² - cable stiffness: rigid |
| Minimum Load Breaking Capacity | 100 operations 1.25 In and 1.1 Un, cos phi = 0.6 |
| Electrical Durability | 10000 cycles, cos phi = 0.8 |
| Insulation Resistance | > 5 MOhm at 500 V |
| Dielectric Strength | 2000 V |
| Material | ASA + PC: mechanism cover PBT (polybutylene terephthalate) GF30: fixing frame ABS (acrylonitrile butadiene-styrene): cover frame |
| Surface Finish | Brilliant |
| Quantity Per Set | Set of 1 plastic bag and cardboard with eurohole |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|-------------------|-----------|
| Embedding Depth | 30 mm |
| Depth | 40 mm |
| Width | 90.21 mm |
| Height | 122.9 mm |
| Surface Treatment | Untreated |

Environment

| | |
|---------------------------------------|-------------------------------------------------------------------------------------------------------|
| Ambient Air Temperature For Operation | 15...30 °C |
| Ambient Air Temperature For Storage | 0...35 °C |
| Ik Degree Of Protection | IK01 |
| Ip Degree Of Protection | IP20 |
| Environmental Characteristic | UV resistant Window-cleaning fluid Liquid soap Oil Bleach Petrol Alcohol Acetone |

Packing Units

| | |
|------------------------------|-----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 5.000 cm |
| Package 1 Width | 8.500 cm |
| Package 1 Length | 12.000 cm |
| Package 1 Weight | 119.300 g |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 5 |
| Package 2 Height | 12.500 cm |
| Package 2 Width | 13.000 cm |
| Package 2 Length | 18.500 cm |
| Package 2 Weight | 650.000 g |
| Unit Type Of Package 3 | S03 |
| Number Of Units In Package 3 | 50 |
| Package 3 Height | 30.000 cm |
| Package 3 Width | 30.000 cm |
| Package 3 Length | 40.000 cm |
| Package 3 Weight | 7.027 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

| | |
|--------------------------|-----------------------------------------------------------------------------------------------------------------------------|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | No need of specific recycling operations |