

Product data sheet

Specifications



Unica - 1 S.O. - 2P+E, shutters, US - 1 m - white

MGU3.028.18

⚠ Discontinued on: Jun 15, 2023

⚠ Discontinued

Main

| | |
|-----------------------------|----------------------------|
| Range | Unica |
| Product Or Component Type | Socket-outlet |
| Aesthetic Name | Unica (standard aesthetic) |
| Device Presentation | Mechanism |
| Device Mounting | Flush |
| Socket Number | 1 |
| Outlet Poles Configuration | 2P + E |
| Outlet Standard | American |
| Outlet Standard Description | Displaced earth |
| Rated Current | 15 A |

Complementary

| | |
|--------------------------------|---|
| Device Application | Power supply |
| Cover Type | With shutter |
| [Ue] Rated Operational Voltage | 127 V |
| Network Type | AC |
| Network Frequency | 50/60 Hz |
| Number Of Modules | 1 module |
| Fixing Mode | Clip-in |
| Colour Tint | White |
| Connections - Terminals | Screw terminals |
| Cable Cross Section | 0...4 mm ² - cable stiffness: flexible 0...4 mm ² - cable stiffness: rigid |
| Minimum Load Breaking Capacity | 100 operations 1.25 In and 1.1 Un, cos phi = 0.6 |
| Electrical Durability | 10000 cycles, cos phi = 0.8 |
| Insulation Resistance | > 5 MOhm at 500 V |
| Dielectric Strength | 2000 V |
| Material | ASA + PC: mechanism cover |
| Quantity Per Set | Set of 1 blister |
| Embedding Depth | 24 mm |
| Depth | 33 mm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------|-----------|
| Width | 22.5 mm |
| Height | 45 mm |
| Net Weight | 0.0235 kg |

Environment

| | |
|---------------------------------------|---|
| Ambient Air Temperature For Operation | 15...30 °C |
| Ambient Air Temperature For Storage | 0...35 °C |
| Ik Degree Of Protection | IK01 |
| Ip Degree Of Protection | IP20 |
| Environmental Characteristic | Oil Liquid soap Alcohol Bleach Acetone UV resistant Petrol Window-cleaning fluid |

Packing Units

| | |
|------------------------------|---------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 4.5 cm |
| Package 1 Width | 6.5 cm |
| Package 1 Length | 6.5 cm |
| Package 1 Weight | 26.0 g |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 10 |
| Package 2 Height | 4.5 cm |
| Package 2 Width | 13.5 cm |
| Package 2 Length | 33.3 cm |
| Package 2 Weight | 262.0 g |
| Unit Type Of Package 3 | S01 |
| Number Of Units In Package 3 | 20 |
| Package 3 Height | 15.0 cm |
| Package 3 Width | 15.0 cm |
| Package 3 Length | 40.0 cm |
| Package 3 Weight | 866.0 g |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | No need of specific recycling operations |