

Product data sheet

Specifications



Unica Top/Class - 1 S.O. - 2P, shutters, EU - 2 m - graphite

MGU3.033.12

 **Discontinued on:** Jun 15, 2023

 **Discontinued**

Main

Range	Unica
Product Or Component Type	Socket-outlet
Aesthetic Name	Unica Top - Unica Class
Device Presentation	Mechanism
Device Mounting	Flush
Socket Number	1
Outlet Poles Configuration	2P
Outlet Standard	European
Rated Current	16 A

Complementary

Device Application	Power supply
Cover Type	With shutter
[Ue] Rated Operational Voltage	250 V
Network Type	AC
Network Frequency	50/60 Hz
Number Of Modules	2 modules
Fixing Mode	Clip-in
Colour Tint	Graphite
Connections - Terminals	Screw terminals
Cable Cross Section	0...4 mm ² - cable stiffness: flexible 0...4 mm ² - cable stiffness: rigid
Minimum Load Breaking Capacity	100 operations 1.25 In and 1.1 Un, cos phi = 0.6
Electrical Durability	10000 cycles, cos phi = 0.8
Insulation Resistance	> 5 MOhm at 500 V
Dielectric Strength	2000 V
Material	ASA + PC: mechanism cover
Quantity Per Set	Set of 1 blister
Product Certifications	FR.ME63.B02375 AC
Embedding Depth	27 mm
Depth	37 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Width	45 mm
Height	45 mm
Net Weight	0.0287 kg

Environment

Ambient Air Temperature For Operation	15...30 °C
Ambient Air Temperature For Storage	0...35 °C
Ik Degree Of Protection	IK01
Ip Degree Of Protection	IP20
Environmental Characteristic	Petrol Oil Window-cleaning fluid Acetone Alcohol UV resistant Liquid soap Bleach

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.800 cm
Package 1 Width	4.400 cm
Package 1 Length	6.700 cm
Package 1 Weight	36.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	4.500 cm
Package 2 Width	13.500 cm
Package 2 Length	33.500 cm
Package 2 Weight	365.0 g
Unit Type Of Package 3	S02
Number Of Units In Package 3	40
Package 3 Height	15.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	1.774 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations