

Product data sheet

Specifications



Unica Top/Class - 1 S.O. (lid) - 2P+E, shutters, DE - 2 m - aluminium

MGU3.037.30TA

⚠ Discontinued on: Jun 15, 2023

⚠ Discontinued

Main

Range	Unica
Product Or Component Type	Socket-outlet
Aesthetic Name	Unica Top - Unica Class
Device Presentation	Mechanism
Device Mounting	Flush
Socket Number	1
Outlet Poles Configuration	2P + E
Outlet Standard	Schuko
Outlet Standard Description	Side earth
Rated Current	16 A

Complementary

Device Application	Power supply
Cover Type	Hinged cover With shutter
[Ue] Rated Operational Voltage	250 V
Network Type	AC
Network Frequency	50/60 Hz
Number Of Modules	2 modules
Fixing Mode	Clip-in
Colour Tint	Aluminium
Connections - Terminals	Screw terminals
Cable Cross Section	0...4 mm ² - cable stiffness: flexible 0...4 mm ² - cable stiffness: rigid
Minimum Load Breaking Capacity	100 operations 1.25 In and 1.1 Un, cos phi = 0.6
Electrical Durability	10000 cycles, cos phi = 0.8
Insulation Resistance	> 5 MOhm at 500 V
Dielectric Strength	2000 V
Material	ASA + PC: mechanism cover
Quantity Per Set	Set of 1 blister
Product Certifications	FR.ME63.B02375 AC 14.10.01/5433

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Embedding Depth	30 mm
Depth	40 mm
Width	45 mm
Height	45 mm
Net Weight	0.0408 kg

Environment

Ambient Air Temperature For Operation	15...30 °C
Ambient Air Temperature For Storage	0...35 °C
Ik Degree Of Protection	IK01
Ip Degree Of Protection	IP20
Environmental Characteristic	Window-cleaning fluid Acetone Liquid soap Alcohol Oil Petrol UV resistant Bleach

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	4.6 cm
Package 1 Length	4.6 cm
Package 1 Weight	40.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	12.7 cm
Package 2 Width	12.4 cm
Package 2 Length	18.5 cm
Package 2 Weight	463.0 g
Unit Type Of Package 3	S02
Number Of Units In Package 3	40
Package 3 Height	15.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	2.17 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations