



Main

Range	Unica
Device application	Power supply
Product or component type	Socket-outlet
Aesthetic name	Unica (standard aesthetic)
Device presentation	Mechanism
Socket number	1
Outlet poles configuration	2P + E with shutters
Outlet standard	French
Outlet standard description	Pin earth

Complementary

Rated current	16 A at 250 V AC
Network frequency	50/60 Hz
Number of modules	2 modules
Fixing mode	Clip-in
Colour tint	Red
Connections - terminals	Screw terminals
Cable cross section	0...4 mm ² - cable stiffness: flexible 0...4 mm ² - cable stiffness: rigid
Minimum load breaking capacity	100 operations 1.25 In and 1.1 Un, cos phi = 0.6
Electrical durability	10000 cycles, cos phi = 0.8
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Material	ASA + PC: mechanism cover
Quantity per set	Set of 1 blister
Product certifications	FR.ME63.B02375 AC
Embedding depth	27 mm
Depth	37 mm
Width	45 mm

Height	45 mm
Net weight	0.0362 kg

Environment

Ambient air temperature for operation	15...30 °C
Ambient air temperature for storage	0...35 °C
IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Window-cleaning fluid Liquid soap Ammonia Bleach UV resistant Oil Alcohol Acetone Petrol
Environmental health and issues	Halogen free

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Under investigation
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------