



Main

Range of product	Unica
Range	Unica
Device application	Power supply
Product or component type	1 socket-outlet
Aesthetic name	Unica
Device presentation	Complete socket-outlet
Outlet poles configuration	2P + E with shutters
Outlet standard	Euroamerican
Socket additional information	Earthed
Decoration colour	White (RAL 9003)
Cover plate colour tint	White (RAL 9003)
Cover frame colour tint	White (RAL 9003)
Quantity per set	Set of 1 blister

Complementary

Rated current	10 A at 250 V AC 50/60 Hz 15 A at 127 V AC 50/60 Hz
Number of modules	1 module
Fixing mode	Clip-in
Connections - terminals	Screw terminals
Cable cross section	4 mm ² flexible cable 4 mm ² rigid cable
Minimum load breaking capacity	100 operations 1.25 I _n and 1.1 I _n , cos phi = 0.6
Electrical durability	10000 cycles, cos phi = 0.8
Insulation resistance	>= 5 MOhm at 500 V
Material	ASA + PC: mechanism cover
Embedding depth	21 mm
Depth	33 mm

Width	22.5 mm
Height	45 mm
Net weight	0.024 kg
Surface treatment	Untreated

Environment

Dielectric strength	2000 V
Ambient air temperature for operation	15...30 °C
Ambient air temperature for storage	0...35 °C
IK degree of protection	IK01
IP degree of protection	IP20
Standards	IEC 60884-1
Environmental characteristic	UV resistant Alcohol Bleach Ammonia Oil Petrol Liquid soap Window-cleaning fluid Acetone

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Under investigation
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------