



## Main

Range of product	Unica
Aesthetic name	Unica (standard aesthetic)
Device application	Control
Product or component type	Switch
Device presentation	Mechanism
Switch function	1-pole 1-way
Provided equipment	Internal power connection
Colour tint	White

## Complementary

Rated current	10 AX, 250 V AC, 50/60 Hz
Electrical durability	10000 cycles
Insulation resistance	> 5 MOhm @500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi: 0.3
Opening distance	> 3 mm
Actuator	Rocker
Number of modules	1 module
Pilot light	Amber LED : 0.15 mA (temperature : 15 °C)
Connections - terminals	Screwless terminals
Cable cross section	0...2.5 mm <sup>2</sup> (rigid) 0...2.5 mm <sup>2</sup> (flexible)
Material	Mechanism cover : ASA + PC
Fixing mode	Clip-in
Width	22.5 mm
Height	45 mm
Depth	34 mm

Embedding depth	22 mm
Product weight	0.0195 kg
Ambient air temperature for operation	25...35 °C
Ambient air temperature for storage	0...50 °C
Standards	EMC directive EN 60669-1 LV directive

## Environment

IP degree of protection	IP20
IK degree of protection	IK01
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid
Environmental health and issues	Halogen free

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0622 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------