



Main

Range of product	Unica
Aesthetic name	Unica (standard aesthetic)
Device application	Control
Product or component type	Switch
Device presentation	Mechanism
Switch function	1-pole 2-way
Provided equipment	Internal power connection
Colour tint	White

Complementary

Rated current	10 AX, 250 V AC, 50/60 Hz
Electrical durability	10000 cycles
Insulation resistance	> 5 MOhm @500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi: 0.3
Opening distance	> 3 mm
Actuator	Rocker
Number of modules	1 module
Connections - terminals	Screw terminals
Cable cross section	0...2.5 mm ² (rigid) 0...2.5 mm ² (flexible)
Material	Mechanism cover : ASA + PC
Fixing mode	Clip-in
Width	22.5 mm
Height	45 mm
Depth	34 mm
Embedding depth	22 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product weight	0.0211 kg
Ambient air temperature for operation	25...35 °C
Ambient air temperature for storage	0...50 °C
Standards	EMC directive EN 60669-1 LV directive

Environment

IP degree of protection	IP20
IK degree of protection	IK01
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid
Environmental health and issues	Halogen free

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0622 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------