



### Main

Range of product	Unica
Aesthetic name	Unica (standard aesthetic)
Product or component type	Switch
Device presentation	Mechanism
Switch function	Intermediate
Device application	Control
Provided equipment	Internal power connection
Colour tint	White

### Complementary

Rated current	10 AX at 250 V AC 50/60 Hz
Electrical durability	10000 cycles
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi = 0.3
Opening distance	> 3 mm
Actuator	Rocker
Number of modules	1 module
Connections - terminals	Screw terminals
Cable cross section	0...2.5 mm <sup>2</sup> rigid cable 0...2.5 mm <sup>2</sup> flexible cable
Material	ASA + PC: mechanism cover
Fixing mode	Clip-in
Width	22.5 mm
Height	45 mm
Depth	34 mm
Embedding depth	22 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

Net weight	0.026 kg
Ambient air temperature for operation	25...35 °C
Ambient air temperature for storage	0...50 °C
Standards	EN 60669-1 EMC directive LV directive

## Environment

IP degree of protection	IP20
IK degree of protection	IK01
Environmental characteristic	Bleach UV resistant Window-cleaning fluid Liquid soap Petrol Acetone Oil Alcohol Ammonia
Environmental health and issues	Halogen free

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Under investigation
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------