



Main

| | |
|---------------------------|----------------------------|
| Range of product | Unica |
| Aesthetic name | Unica (standard aesthetic) |
| Device application | Bell switch |
| Product or component type | Switch |
| Device presentation | Mechanism |
| Switch function | 1-pole 1-way |
| Colour tint | Ivory |

Complementary

| | |
|--------------------------------|---------------------------------------------------------------------------------------|
| Rated current | 10 A, 250 V AC, 50/60 Hz |
| Electrical durability | 40000 cycles (cos phi: 0.6) |
| Insulation resistance | > 5 MOhm @500 V |
| Dielectric strength | 2000 V |
| Minimum load breaking capacity | 200 operations 1.25 In and 1.1 Un, cos phi: 0.3 |
| Condition of use | Impulse relay control |
| Opening distance | > 3 mm |
| Actuator | Push-button |
| Number of modules | 1 module |
| Connections - terminals | Screwless terminals |
| Cable cross section | 0...2.5 mm ² (rigid) 0...2.5 mm ² (flexible) |
| Material | Mechanism cover : ASA + PC Mechanism cover : ABS (acrylonitrile butadiene-styrene) |
| Marking | Bell symbol |
| Fixing mode | Clip-in |
| Width | 22.5 mm |
| Height | 45 mm |
| Depth | 34 mm |

| | |
|---------------------------------------|---------------------------------------------|
| Embedding depth | 22 mm |
| Product weight | 0.0173 kg |
| Ambient air temperature for operation | 25...35 °C |
| Ambient air temperature for storage | 0...50 °C |
| Standards | EMC directive EN 60669-1 LV directive |

Environment

| | |
|---------------------------------|------------------------------------------------------------------------------------------------------------------|
| IP degree of protection | IP20 |
| IK degree of protection | IK01 |
| Environmental characteristic | Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid |
| Environmental health and issues | Halogen free |

Offer Sustainability

| | |
|----------------------------------|---------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 0622 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product environmental profile | Available Product Environmental Profile |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|