



Main

Range	Unica
Device application	Control
Product or component type	Switch
Aesthetic name	Unica (standard aesthetic)
Device presentation	Mechanism
Switch function	2-way
Switch application	Roller blind
Rated current	10 AX, 250 V AC, 50/60 Hz
Actuator	Rocker
Number of modules	1 module
Fixing mode	Clip-in
Cover plate colour tint	Ivory

Complementary

Contacts type and composition	1 C/O
Mechanical interlocking	Interlock between up/down
[Iu] rated interrupted current	Motor : 2.5 A
Opening distance	> 3 mm
Marking	UP Down
Connections - terminals	Screw terminals
Cable cross section	<= 2.5 mm ² (flexible) <= 2.5 mm ² (rigid)
Minimum load breaking capacity	200 operations 1.25 I _n and 1.1 I _{un} , cos phi: 0.3
Electrical durability	10000 cycles (cos phi: 0.6)
Insulation resistance	> 5 MOhm @500 V
Dielectric strength	> 2000 V
Material	Mechanism cover : ASA + PC

Standards	LV directive EMC directive EN 60669-1
Ambient air temperature for operation	25...35 °C
Ambient air temperature for storage	0...50 °C
Embedding depth	21 mm
Depth	33 mm
Width	22.4 mm
Height	45 mm
Product weight	0.0382 kg

Environment

IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Petrol Oil Alcohol Window-cleaning fluid Liquid soap UV resistant Ammonia Bleach Acetone
Environmental health and issues	Halogen free

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1834 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------