


Product data sheet

Specifications



Unica - push-button - 1-way - 10 A 12 V AC - 2 m - ivory

MGU3.216.25CN

 **Discontinued on:** Dec 15, 2021

 **Discontinued**

Main

| | |
|---------------------------|----------------------------|
| Range Of Product | Unica |
| Aesthetic Name | Unica (standard aesthetic) |
| Product Or Component Type | Push-button |
| Device Presentation | Mechanism |
| Technology Type | Electromechanical |
| Switch Function | 1-pole 1-way |
| Number Of Rocker | 1 |
| Device Application | Bell switch |
| Colour Tint | Ivory |

Complementary

| | |
|--------------------------------|--|
| Rated Current | 10 A |
| [Ue] Rated Operational Voltage | 12 V |
| Network Type | AC |
| Network Frequency | 50/60 Hz |
| Electrical Durability | 40000 cycles, cos phi = 0.6 |
| Insulation Resistance | > 5 MOhm at 500 V |
| Dielectric Strength | 2000 V |
| Minimum Load Breaking Capacity | 200 operations 1.25 In and 1.1 Un, cos phi = 0.3 |
| Condition Of Use | Impulse relay control |
| Opening Distance | > 3 mm |
| Actuator | Push-button |
| Number Of Modules | 2 modules |
| Pilot Light | LED, colour: blue, current consumption: 0.15 mA, temperature rise: 15 °C |
| Connections - Terminals | Screwless terminals |
| Cable Cross Section | 0...2.5 mm² rigid cable 0...2.5 mm² flexible cable |
| Material | ASA + PC: mechanism cover |
| Marking | Bell symbol |
| Fixing Mode | Clip-in |
| Width | 45 mm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|---------------------------------------|---|
| Height | 45 mm |
| Depth | 34 mm |
| Embedding Depth | 22 mm |
| Net Weight | 0.027 kg |
| Ambient Air Temperature For Operation | 25...35 °C |
| Ambient Air Temperature For Storage | 0...50 °C |
| Standards | EMC directive LV directive EN 60669-1 |

Environment

| | |
|------------------------------|---|
| Ip Degree Of Protection | IP20 |
| Ik Degree Of Protection | IK01 |
| Environmental Characteristic | UV resistant Oil Bleach Window-cleaning fluid Liquid soap Acetone Petrol Alcohol |

Packing Units

| | |
|------------------------------|--------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 6.7 cm |
| Package 1 Width | 4.4 cm |
| Package 1 Length | 6.8 cm |
| Package 1 Weight | 29 g |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | No need of specific recycling operations |