


Product data sheet

Specifications



Unica Top/Class - 1 RJ45 socket (S-One) - 1 m - Cat.6, UTP - graph.

MGU3.414.12

 **Discontinued on:** Dec 31, 2023

 **Discontinued**

Main

Range	Unica
Aesthetic Name	Unica Top - Unica Class
Product Or Component Type	Data socket
Device Application	Communication
Device Presentation	Mechanism
Colour Tint	Graphite
Data Socket Type	RJ45 4 contact(s) Cat.6 < 250 MHz
Provided Equipment	Label holder Protective flap

Complementary

Communication Network Type	1000BASE-TX
Communication Port Protocol	ATM 1200 Mbps
Product Destination	Floor box Duct
Number Of Modules	1 module
Socket Number	1
Type Of Footprint	Infraplus
Connector Type	S-One
Cable Shielding Type	U/UTP
Organization Of Wire	Unshielded twisted pair
Connections - Terminals	Click
Device Mounting	Flush
Fixing Mode	Clip-in By clips: shield
Installation Direction	Straight
Material	ABS (acrylonitrile butadiene-styrene): mechanism cover
Depth	36 mm
Width	22.5 mm
Height	45 mm
Embedding Depth	25 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK01
Ambient Air Temperature For Operation	15...30 °C
Ambient Air Temperature For Storage	0...35 °C
Environmental Characteristic	Liquid soap Alcohol Oil UV resistant Petrol Bleach Acetone Window-cleaning fluid
Standards	ISO 8877

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.9 cm
Package 1 Width	2.3 cm
Package 1 Length	4.5 cm
Package 1 Weight	20.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	5.5 cm
Package 2 Width	11.0 cm
Package 2 Length	24.7 cm
Package 2 Weight	254.0 g
Unit Type Of Package 3	S02
Number Of Units In Package 3	60
Package 3 Height	15.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	2.0 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Toxic Heavy Metal Free	
 Mercury Free	
 Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations