



Main

Range	Unica
Aesthetic name	Unica (standard aesthetic)
Product or component type	RJ45 connector
Device application	Communication
Device presentation	Mechanism with central plate
Colour tint	Ivory
Data socket type	RJ45 - 4 contacts - category 6 - transmission rate < 250 MHz
Provided equipment	Label holder Protective flap

Complementary

Communication network type	1000BASE-TX
Communication port protocol	ATM 1200 Mbps
Product destination	Floor box Duct
Number of modules	1 module
Socket number	1
Type of footprint	Infraplus
Connector type	S-One
Cable shielding type	U/UTP
Organization of wire	Unshielded twisted pair
Connections - terminals	Click
Device mounting	Flush
Fixing mode	For shield : by clips Clip-in
Installation direction	Straight
Material	Mechanism cover : ASA + PC
Depth	36 mm
Width	22.5 mm
Height	45 mm
Embedding depth	25 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

IP degree of protection	IP40
IK degree of protection	IK01
Ambient air temperature for operation	15...30 °C
Ambient air temperature for storage	0...35 °C
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid
Environmental health and issues	Halogen free
Standards	ISO 8877

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0844 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------