

# Product data sheet

Specifications



## Unica - 1 RJ45 socket (S-One) - 1 m - Cat.6, S/FTP - white

MGU3.416.18

 **Discontinued on:** Feb 29, 2024

 **Discontinued**

### Main

Range	Unica
Aesthetic Name	Unica (standard aesthetic)
Product Or Component Type	Data socket
Device Application	Communication
Device Presentation	Mechanism
Colour Tint	White (RAL 9003)
Data Socket Type	RJ45 4 contact(s) Cat.6 < 250 MHz
Provided Equipment	Protective flap Label holder

### Complementary

Communication Network Type	1000BASE-TX
Communication Port Protocol	ATM 1200 Mbps
Product Destination	Floor box Duct
Number Of Modules	1 module
Socket Number	1
Type Of Footprint	Infraplus
Connector Type	S-One
Cable Shielding Type	S/FTP
Organization Of Wire	Shielded twisted pair
Connections - Terminals	Click
Device Mounting	Flush
Fixing Mode	Clip-in By clips: shield
Installation Direction	Straight
Material	ASA + PC: mechanism cover
Depth	36 mm
Width	22.5 mm
Height	45 mm
Embedding Depth	25 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK01
Ambient Air Temperature For Operation	15...30 °C
Ambient Air Temperature For Storage	0...35 °C
Environmental Characteristic	Window-cleaning fluid Bleach Oil Liquid soap Alcohol UV resistant Petrol Acetone
Standards	ISO 8877

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.6 cm
Package 1 Width	7.3 cm
Package 1 Length	7.3 cm
Package 1 Weight	44 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	5.6 cm
Package 2 Width	11 cm
Package 2 Length	24.7 cm
Package 2 Weight	484 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	170
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	8.7 kg

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

 Toxic Heavy Metal Free

 Mercury Free

Eu Rohs Directive	Under investigation
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations