



Main

Range	Unica
Product or component type	USB connector
Connector type	USB 2.0
Electrical circuit type	Data
Device presentation	Mechanism
Colour tint	White (RAL 9003)
Type of packing	Group

Complementary

Device mounting	Flush
Fixing mode	Clip-in
Quantity per set	Set of 10
Sale per indivisible quantity	1
Connections - terminals	Screw terminals
Clamping connection capacity	<= 1.5 mm ² for stranded cable(s) <= 1.5 mm ² for flexible cable(s) <= 1.5 mm ² for rigid cable(s)
Wire stripping length	8 mm
Material	Thermoplastic ABS-UV stabilised: centre plate PC (polycarbonate) GF10 FR: casing
Height	45 mm
Width	22.5 mm
Depth	28.3 mm
Embedding depth	19.7 mm
Net weight	0.0141 kg

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	-5...40 °C
Standards	IEC 998-2-1 IEC 998-1
IP degree of protection	IP21

IK degree of protection	IK04
Environmental characteristic	Acetone Oil UV resistant Liquid soap Petrol Window-cleaning fluid Bleach Alcohol Ammonia
Environmental health and issues	Halogen free

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------