



Main

Range	Unica
Aesthetic name	Unica (standard aesthetic)
Product or component type	RJ45 connector
Device presentation	Mechanism
Colour tint	Ivory (RAL 9010)
Data socket type	RJ45 8 contact(s) Cat.6A < 500 MHz
Provided equipment	Label holder Protective flap

Complementary

Communication network type	10GBASE-T
Communication port protocol	ATM 1200 Mbps
Number of modules	1 module
Socket number	1
Type of footprint	Infraplus
Connector type	S-One
Cable shielding type	U/UTP
Organization of wire	Unshielded twisted pair
Connections - terminals	Click
Fixing mode	Clip-in
Material	ASA + PC: mechanism cover
Depth	36 mm
Width	22.5 mm
Height	45 mm
Embedding depth	25 mm

Environment

IP degree of protection	IP40
IK degree of protection	IK01
Ambient air temperature for operation	15...30 °C
Ambient air temperature for storage	0...35 °C

Environmental characteristic	Liquid soap Acetone Window-cleaning fluid Alcohol UV resistant Bleach Oil Ammonia Petrol
Environmental health and issues	Halogen free
Standards	ISO 8877

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Under investigation
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information

Contractual warranty

Warranty	18 months
----------	-----------