

Product data sheet

Specifications



Unica Top/Class - 1 RJ45 socket (S-One) - 2 m - Cat.6_A, UTP - graph.

MGU3.445.12

 **Discontinued on:** Dec 31, 2016

 **Discontinued**

Main

Range	Unica
Aesthetic Name	Unica Top - Unica Class
Product Or Component Type	Data socket
Device Presentation	Mechanism
Colour Tint	Graphite
Data Socket Type	RJ45 8 contact(s) Cat.6 _A < 500 MHz
Provided Equipment	Protective flap Label holder

Complementary

Communication Network Type	10GBASE-T
Communication Port Protocol	ATM 1200 Mbps
Number Of Modules	2 modules
Socket Number	1
Type Of Footprint	Infraplus
Connector Type	S-One
Cable Shielding Type	U/UTP
Organization Of Wire	Unshielded twisted pair
Connections - Terminals	Click
Fixing Mode	Clip-in
Installation Direction	Straight
Material	ABS (acrylonitrile butadiene-styrene): mechanism cover
Depth	36 mm
Width	85 mm
Height	80 mm
Embedding Depth	25 mm

Environment

Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK01
Ambient Air Temperature For Operation	15...30 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Storage	0...35 °C
Environmental Characteristic	Bleach Oil Liquid soap Acetone UV resistant Window-cleaning fluid Petrol Alcohol
Standards	ISO 8877

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.6 cm
Package 1 Width	4.5 cm
Package 1 Length	4 cm
Package 1 Weight	20 g

Contractual warranty

Warranty	18 months
----------	-----------