

Product data sheet

Characteristics

MGU3.447.30

Unica Top/Class - 1 RJ45 socket (S-One) - 2 m -
Cat.6A, S/FTP - alu.



Main

Range	Unica
Aesthetic name	Unica Top - Unica Class
Product or component type	RJ45 connector
Device presentation	Mechanism
Colour tint	Aluminium
Data socket type	RJ45 8 contact(s) Cat.6A < 500 MHz
Provided equipment	Protective flap Label holder

Complementary

Communication network type	10GBASE-T
Communication port protocol	ATM 1200 Mbps
Number of modules	2 modules
Socket number	1
Type of footprint	Infraplus
Connector type	S-One
Cable shielding type	S/FTP
Organization of wire	Shielded twisted pair
Connections - terminals	Click
Fixing mode	Clip-in
Material	ABS (acrylonitrile butadiene-styrene): mechanism cover
Depth	36 mm
Width	85 mm
Height	80 mm
Embedding depth	25 mm

Environment

IP degree of protection	IP40
IK degree of protection	IK01
Ambient air temperature for operation	15...30 °C
Ambient air temperature for storage	0...35 °C

Environmental characteristic	Liquid soap UV resistant Ammonia Alcohol Petrol Window-cleaning fluid Acetone Oil Bleach
Environmental health and issues	Halogen free
Standards	ISO 8877

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------