



Main

Range of product	Unica
Aesthetic name	Unica KNX
Product or component type	Switch
Device presentation	Mechanism
Bus type	KNX
Switch function	1-pole 2-way
Number of rocker	2
Device application	Control
Colour tint	Graphite

Complementary

Rated current	10 A at 24 V DC
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Actuator	Push-button
Number of modules	2 modules
Pilot light	LED, colour: blue, current consumption: 1 mA, temperature rise: 15 °C
Connections - terminals	Screwless terminals
Cable cross section	0...2.5 mm ² rigid cable 0...2.5 mm ² flexible cable
Material	Plastic
Surface finish	Varnished
Device mounting	Flush
Fixing mode	Clip-in
Depth	38 mm
Embedding depth	13 mm
Ambient air temperature for operation	-5...45 °C
Standards	EMC directive

Environment

IP degree of protection	IP20
Environmental characteristic	Liquid soap Petrol Window-cleaning fluid Acetone Ammonia Oil UV resistant Alcohol Bleach
Environmental health and issues	Halogen free

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Under investigation
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations End of Life Information

Contractual warranty

Warranty	18 months
----------	-----------