



### Main

Range	Unica
Aesthetic name	Unica KNX
Product or component type	Switch
Device application	Control
Device presentation	Mechanism
Bus type	KNX
Sensor type	Infrared sensor
Cover plate colour tint	Graphite

### Complementary

Rated current	10 A at 250 V AC 50/60 Hz
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Number of modules	2 modules
Switch function	2-way
Contacts type and composition	2 NO
Opening distance	> 3 mm
Transmission support medium	Infrared
Actuator	Push-button
Pilot light	LED, colour: blue, current consumption: 1 mA, temperature rise: 15 °C
Connections - terminals	Screwless terminals
Cable cross section	2.5 mm <sup>2</sup> flexible cable 2.5 mm <sup>2</sup> rigid cable
Material	Plastic
Surface finish	Varnished Brilliant
Device mounting	Flush
Fixing mode	Screws

## Environment

IP degree of protection	IP20
IK degree of protection	IK01
Ambient air temperature for operation	-5...45 °C
Environmental characteristic	Bleach Ammonia Oil Liquid soap Acetone UV resistant Petrol Window-cleaning fluid Alcohol
Environmental health and issues	Halogen free
Standards	EMC directive LV directive

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Under investigation
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations <a href="#">End of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------