

Product data sheet

Specifications



Unica KNX - infrared pushbutton - 2-way - 10 A, 250 VAC - 2 m - white

MGU3.532.18

 **Discontinued on:** Jun 15, 2023

 **Discontinued**

Main

Range	Unica
Aesthetic Name	Unica KNX
Product Or Component Type	Switch
Device Application	Control
Device Presentation	Mechanism
Bus Type	KNX
Sensor Type	Infrared sensor
Cover Plate Colour Tint	White (RAL 1013)

Complementary

Rated Current	10 A at 250 V AC 50/60 Hz
Insulation Resistance	> 5 MOhm at 500 V
Dielectric Strength	2000 V
Number Of Modules	2 modules
Switch Function	2-way
Contacts Type And Composition	2 NO
Opening Distance	> 3 mm
Transmission Support Medium	Infrared
Actuator	Push-button
Pilot Light	LED, colour: blue, current consumption: 1 mA, temperature rise: 15 °C
Connections - Terminals	Screwless terminals
Cable Cross Section	2.5 mm² flexible cable 2.5 mm² rigid cable
Material	Plastic
Surface Finish	Brilliant
Device Mounting	Flush
Fixing Mode	Screws

Environment

Ip Degree Of Protection	IP20
Ik Degree Of Protection	IK01

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Operation	-5...45 °C
Environmental Characteristic	Bleach Alcohol UV resistant Window-cleaning fluid Petrol Acetone Liquid soap Oil
Standards	EMC directive LV directive

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	9.5 cm
Package 1 Length	9.5 cm
Package 1 Weight	94.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	24
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.04 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations Circularity Profile