

# Product data sheet

Specifications



## Unica KNX - movement detector - 230 VAC - 2 m - white

MGU3.533.18

⚠ Discontinued on: Sep 30, 2023

⚠ Discontinued

### Main

Range	Unica
Aesthetic Name	Unica KNX
Product Or Component Type	Movement detector
Device Application	Lighting
Device Presentation	Mechanism
Product Specific Application	Staircase monitoring
Bus Type	KNX
Cover Plate Colour Tint	White (RAL 1013)

### Complementary

[Ue] Rated Operational Voltage	230 V AC +/- 10 % at 50/60 Hz
Movement Detection Area	9 x 9 m(PIR mounting height 2.15m)
Detection Face	Lateral: 9 m
Horizontal Detection Angle	0...180 °
Number Of Modules	2 modules
Type Of Setting	Light sensitivity adjustable
Light Intensity Adjustment	10...1000 lux rotary switch 10...2000 lux ETS
Time Delay Range	1 s...8 min (rotary switch) 1 s...255 h (ETS)
Duty Cycle	15300 minutes
Clamping Connection Capacity	<= 2 x 2.5 mm² for flexible cable(s) <= 2 x 2.5 mm² for rigid cable(s)
Connections - Terminals	Screwless terminals
Material	ASA + PC: mechanism cover Zamak: fixing frame
Surface Finish	Brilliant
Device Mounting	Flush
Fixing Mode	Clip-in
Mounting Height	1...2.15 m
Depth	56 mm
Embedding Depth	34 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Ip Degree Of Protection	IP20
Ambient Air Temperature For Operation	-5...45 °C
Environmental Characteristic	Window-cleaning fluid Alcohol Acetone Petrol Oil UV resistant Bleach Liquid soap
Standards	EMC directive LV directive

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	9.5 cm
Package 1 Length	9.5 cm
Package 1 Weight	111.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	24
Package 2 Height	18.5 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.07 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>