



Main

Range of product	Unica Wireless
Product or component type	Combined roller blind
Device presentation	Mechanism
Transmission frequency	868.3 MHz
[Ue] rated operational voltage	110/230 V AC (+/- 10 %), 50/60 Hz
Number of modules	2 modules
Fixing mode	Claws
Colour tint	Graphite
Device composition	1 large rocker and 2 narrow rockers Wireless emitter and receiver
Provided equipment	Set of 4 symbols

Complementary

Wiring device mounting	Flush
Operating distance	Indoor : 10...50 m Outdoor : <= 300 m
Load type	Motor : 690 W
Protection type	Fuse protection
Connections - terminals	Screw terminals
Clamping connection capacity	<= 2 x 2.5 mm ² for flexible cable(s) <= 2 x 2.5 mm ² for rigid cable(s)
Type of setting	Neutral position
Standards	99/5/EEC EN 60669-1 EN 60669-2-1 89/336/EEC ETSI EN 301 489 ETSI EN 300 220
Ambient air temperature for operation	-5...50 °C
Relative humidity	20...95 %

Embedding depth	34 mm
Depth	46 mm

Environment

IP degree of protection	IP20
Environmental characteristic	UV resistant Acetone Liquid soap Window-cleaning fluid Oil Bleach Ammonia Petrol Alcohol
Environmental health and issues	Halogen free

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1342 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference contains SVHC above the threshold - Go to CaP for more details Go to CaP for more details
Product environmental profile	Available Product Environmental Profile

Contractual warranty

Warranty period	18 months
-----------------	-----------