

Product data sheet

Specifications



Unica Top/Class - fuse holder - 10 A, 250 VAC - cyl. 6x32 mm - 1 m - graph.

MGU3.630.12

! Discontinued

! Discontinued on: Apr 5, 2017

! End-of-service on: Sep 1, 2017

Main

Range	Unica
Device Application	Safety
Product Or Component Type	Fuse holder
Aesthetic Name	Unica Top - Unica Class
Device Presentation	Mechanism
Rated Current	10 A
[Ue] Rated Operational Voltage	230 V
Network Type	AC
Network Frequency	50/60 Hz
Number Of Modules	1 module
Fixing Mode	Clip-in
Colour Tint	Graphite

Complementary

Fuse Type	Cylindrical 6 x 32 mm
Provided Equipment	Fuse not supplied
Connections - Terminals	Screw terminals
Cable Cross Section	0...4 mm² flexible cable 0...4 mm² rigid cable
Material	ASA + PC: mechanism cover
Standards	UNE 60127
Product Certifications	ES.ME01.B02318 AC
Ambient Air Temperature For Operation	15...30 °C
Ambient Air Temperature For Storage	0...35 °C
Embedding Depth	30.8 mm
Depth	43.5 mm
Width	22.5 mm
Height	45 mm
Net Weight	0.0278 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

<hr/>	
Ik Degree Of Protection	IK01
<hr/>	
Ip Degree Of Protection	IP20
<hr/>	
Environmental Characteristic	Bleach Liquid soap UV resistant Oil Acetone Window-cleaning fluid Alcohol Petrol

Packing Units

<hr/>	
Unit Type Of Package 1	PCE
<hr/>	
Number Of Units In Package 1	1
<hr/>	
Package 1 Height	6.7 cm
<hr/>	
Package 1 Width	4.4 cm
<hr/>	
Package 1 Length	6.8 cm
<hr/>	
Package 1 Weight	38 g

Contractual warranty

<hr/>	
Warranty	18 months