

Product data sheet

Specifications



Unica Top/Class - fuse holder - 16 A, 250 VAC - cyl. 8.3x31.5 mm - 2 m - alu.

MGU3.631.30

 **Discontinued on:** Dec 19, 2017

 **Discontinued**

Main

Range	Unica
Device Application	Safety
Product Or Component Type	Fuse holder
Aesthetic Name	Unica Top - Unica Class
Device Presentation	Mechanism
Rated Current	16 A
[Ue] Rated Operational Voltage	230 V
Network Type	AC
Network Frequency	50/60 Hz
Number Of Modules	2 modules
Fixing Mode	Clip-in
Colour Tint	Aluminium

Complementary

Fuse Type	Cylindrical 8.3 x 31.5 mm
Provided Equipment	Fuse not supplied
Connections - Terminals	Screw terminals
Cable Cross Section	0...4 mm² flexible cable 0...4 mm² rigid cable
Material	ASA + PC: mechanism cover
Standards	EN 60269
Ambient Air Temperature For Operation	15...30 °C
Ambient Air Temperature For Storage	0...35 °C
Embedding Depth	31 mm
Depth	44 mm
Width	45 mm
Height	45 mm
Net Weight	0.0292 kg

Environment

Ik Degree Of Protection	IK01
-------------------------	------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ip Degree Of Protection	IP20
Environmental Characteristic	Window-cleaning fluid UV resistant Bleach Liquid soap Oil Petrol Alcohol Acetone

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.7 cm
Package 1 Width	4.8 cm
Package 1 Length	6.8 cm
Package 1 Weight	25 g

Contractual warranty

Warranty	18 months
----------	-----------