

Product data sheet

Specifications



Unica - 1 S.O. (frame) - 2P+E, shutters, DE - 2 m - ivory

MGU5.037.25ZD

⚠ Discontinued on: Jun 15, 2023

⚠ Discontinued

Main

Range	Unica
Product Or Component Type	Socket-outlet
Aesthetic Name	Unica (standard aesthetic)
Device Presentation	Mechanism with zamak fixing frame
Device Mounting	Flush
Socket Number	1
Outlet Poles Configuration	2P + E
Outlet Standard	Schuko
Outlet Standard Description	Side earth
Rated Current	16 A

Complementary

Device Application	Power supply
Cover Type	With shutter
[Ue] Rated Operational Voltage	250 V
Network Type	AC
Network Frequency	50/60 Hz
Number Of Modules	2 modules
Fixing Mode	Screws
Colour Tint	Cream (RAL 9010)
Connections - Terminals	Screw terminals
Cable Cross Section	0...4 mm ² - cable stiffness: flexible 0...4 mm ² - cable stiffness: rigid
Minimum Load Breaking Capacity	100 operations 1.25 In and 1.1 Un, cos phi = 0.6
Electrical Durability	10000 cycles, cos phi = 0.8
Insulation Resistance	> 5 MOhm at 500 V
Dielectric Strength	2000 V
Material	PA (polyamide) 6: mechanism cover Zamak: fixing frame
Surface Finish	Brilliant
Quantity Per Set	Set of 1 film

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product Certifications	FR.ME63.B02375 AC
Embedding Depth	30 mm
Depth	40 mm
Width	70.9 mm
Height	70.9 mm
Net Weight	0.0695 kg
Surface Treatment	Untreated

Environment

Ambient Air Temperature For Operation	15...30 °C
Ambient Air Temperature For Storage	0...35 °C
Ik Degree Of Protection	IK01
Ip Degree Of Protection	IP20
Environmental Characteristic	Liquid soap Bleach UV resistant Window-cleaning fluid Acetone Alcohol Oil Petrol

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	7.500 cm
Package 1 Length	7.500 cm
Package 1 Weight	61.300 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	8.000 cm
Package 2 Width	20.000 cm
Package 2 Length	22.500 cm
Package 2 Weight	707.000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	110
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	8.421 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations