

Product data sheet

Specifications



Unica - rocker switch - 2-way - 10 AX 250 VAC - 2 m - white

MGU5.203.18ZD

⚠ Discontinued on: Jun 15, 2023

⚠ Discontinued

Main

Range Of Product	Unica
Aesthetic Name	Unica (standard aesthetic)
Product Or Component Type	Switch
Device Presentation	Mechanism with fixing frame
Technology Type	Electromechanical
Switch Function	1-pole 2-way
Number Of Rocker	1
Device Application	Light control
Provided Equipment	Internal power connection
Colour Tint	White (RAL 9003)

Complementary

Rated Current	10 AX
[Ue] Rated Operational Voltage	250 V
Network Type	AC
Network Frequency	50/60 Hz
Electrical Durability	10000 cycles
Insulation Resistance	> 5 MOhm at 500 V
Dielectric Strength	2000 V
Minimum Load Breaking Capacity	200 operations 1.25 In and 1.1 Un, cos phi = 0.3
Opening Distance	> 3 mm
Actuator	Rocker
Number Of Modules	2 modules
Connections - Terminals	Screwless terminals
Cable Cross Section	0...2.5 mm² rigid cable 0...2.5 mm² flexible cable
Material	ASA + PC: mechanism cover Zamak: fixing frame
Surface Finish	Untreated
Fixing Mode	Screws
Width	70.9 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Height	70.9 mm
Depth	34 mm
Embedding Depth	24 mm
Net Weight	0.0574 kg
Ambient Air Temperature For Operation	25...35 °C
Ambient Air Temperature For Storage	0...50 °C
Standards	EN 60669-1 EMC directive LV directive
Product Certifications	FR.ME63.B02736

Environment

Ip Degree Of Protection	IP20
Ik Degree Of Protection	IK01
Environmental Characteristic	Oil Bleach Petrol Alcohol UV resistant Acetone Liquid soap Window-cleaning fluid

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	7.5 cm
Package 1 Length	7.5 cm
Package 1 Weight	48 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	8 cm
Package 2 Width	20 cm
Package 2 Length	22.5 cm
Package 2 Weight	596 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	50
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	3.377 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations