

# Product data sheet

Specifications



## Unica - 1 RJ45 socket (S-One) - 2 m - Cat.6, UTP - white

MGU5.415.18ZD

⚠ Discontinued on: Dec 31, 2017

⚠ Discontinued

### Main

Range	Unica
Aesthetic Name	Unica (standard aesthetic)
Product Or Component Type	Data socket
Device Presentation	Mechanism with fixing frame
Colour Tint	White (RAL 9003)
Data Socket Type	RJ45 8 contact(s) Cat.6 < 250 MHz
Provided Equipment	Label holder Protective flap

### Complementary

Communication Network Type	1000BASE-TX
Communication Port Protocol	ATM 1200 Mbps
Number Of Modules	2 modules
Socket Number	1
Type Of Footprint	Infraplus
Connector Type	S-One
Cable Shielding Type	U/UTP
Organization Of Wire	Unshielded twisted pair
Connections - Terminals	Click
Fixing Mode	Screws
Installation Direction	Straight
Material	ASA + PC: mechanism cover Zamak: fixing frame
Depth	36 mm
Width	70.9 mm
Height	70.9 mm
Embedding Depth	25 mm

### Environment

Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK01

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Operation	15...30 °C
Ambient Air Temperature For Storage	0...35 °C
Environmental Characteristic	Liquid soap Alcohol UV resistant Bleach Oil Petrol Acetone Window-cleaning fluid
Standards	ISO 8877

## Contractual warranty

Warranty	18 months
----------	-----------