

Product data sheet

Specifications



Unica - 1 RJ45 socket (S-One) - 2 m - Cat.5e, UTP - white

MGU5.421.18ZD

⚠ Discontinued on: Jun 15, 2023

⚠ Discontinued

Main

Range	Unica
Aesthetic Name	Unica (standard aesthetic)
Product Or Component Type	Data socket
Device Application	Communication
Device Presentation	Mechanism with fixing frame
Colour Tint	White (RAL 9003)
Data Socket Type	RJ45 4 contact(s) Cat.5e < 155 MHz
Provided Equipment	Protective flap Label holder

Complementary

Communication Network Type	1000BASE-T
Communication Port Protocol	ATM 155 Mbps
Number Of Modules	2 modules
Socket Number	1
Type Of Footprint	Infraplus
Connector Type	S-One
Cable Shielding Type	U/UTP
Organization Of Wire	Unshielded twisted pair
Connections - Terminals	Click
Marking	Colour coding
Device Mounting	Flush
Fixing Mode	Screws By screw: shield
Installation Direction	Straight
Material	ASA + PC: mechanism cover Zamak: fixing frame
Depth	36 mm
Width	70.9 mm
Height	70.9 mm
Embedding Depth	25 mm
Net Weight	0.051 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK01
Ambient Air Temperature For Operation	15...30 °C
Ambient Air Temperature For Storage	0...35 °C
Environmental Characteristic	Acetone Bleach Window-cleaning fluid Liquid soap Alcohol Petrol UV resistant Oil
Standards	ISO 8877

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.500 cm
Package 1 Width	7.000 cm
Package 1 Length	7.000 cm
Package 1 Weight	48.300 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	7.500 cm
Package 2 Width	20.000 cm
Package 2 Length	22.500 cm
Package 2 Weight	585.000 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	50
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	3.336 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	No need of specific recycling operations