



### Main

Aesthetic name	Unica (standard aesthetic)
Product or component type	Data/telephone socket
Device presentation	Mechanism with zamak fixing frame + long claws
Telephone socket type	RJ11 (4 contacts): cat.3 (rate: 16 Mbit/s)
Communication network type	ATM 155 Mbps Ethernet 1000BASE-T
Data socket type	RJ45 (8), Cat.5e (transmission rate: <= 100 MHz)
Number of modules	2 modules
Fixing mode	Long claws
Cover plate colour tint	White (RAL 9003)

### Complementary

Type of footprint	Infraplus
Connector type	S-One
Cable shielding type	U/UTP
Organization of wire	Unshielded twisted pair
Connections - terminals	Click
Material	Mechanism cover: ASA + PC Fixing frame: zamak
Standards	ISO 8877
Ambient air temperature for operation	15...30 °C
Ambient air temperature for storage	0...35 °C
Embedding depth	24.6 mm
Depth	35.8 mm
Width	70.9 mm
Height	70.9 mm
Product weight	0.0647 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

## Environment

IK degree of protection	IK01
IP degree of protection	IP40
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0852 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------