

# Product data sheet

Specifications



## Unica Top/Class - 2 RJ45 socket (S-One) - 2x1 m - Cat.6, UTP - graph.

MGU50.2424.12Z

⚠ Discontinued on: Jun 15, 2023

⚠ Discontinued

### Main

Range	Unica
Aesthetic Name	Unica Top - Unica Class
Product Or Component Type	Data socket
Device Presentation	Mechanism with fixing frame
Colour Tint	Graphite
Data Socket Type	RJ45 8 contact(s) Cat.6 < 250 MHz
Provided Equipment	Label holder Protective flap

### Complementary

Communication Network Type	1000BASE-TX
Communication Port Protocol	ATM 1200 Mbps
Number Of Modules	2 x 1 modules
Socket Number	2
Type Of Footprint	Infraplus
Connector Type	S-One
Cable Shielding Type	U/UTP
Organization Of Wire	Unshielded twisted pair
Connections - Terminals	Click
Fixing Mode	Long claws
Installation Direction	Straight
Material	ABS (acrylonitrile butadiene-styrene): mechanism cover Zamak: fixing frame
Depth	36 mm
Width	70.9 mm
Height	70.9 mm
Embedding Depth	25 mm
Net Weight	0.087 kg

### Environment

Ip Degree Of Protection	IP40
-------------------------	------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

<b>Ik Degree Of Protection</b>	IK01
<b>Ambient Air Temperature For Operation</b>	15...30 °C
<b>Ambient Air Temperature For Storage</b>	0...35 °C
<b>Environmental Characteristic</b>	Petrol Bleach Liquid soap Alcohol Oil UV resistant Window-cleaning fluid Acetone
<b>Standards</b>	ISO 8877

## Packing Units

<b>Unit Type Of Package 1</b>	PCE
<b>Number Of Units In Package 1</b>	1
<b>Package 1 Height</b>	7.5 cm
<b>Package 1 Width</b>	7.5 cm
<b>Package 1 Length</b>	3.6 cm
<b>Package 1 Weight</b>	68.0 g
<b>Unit Type Of Package 2</b>	CAR
<b>Number Of Units In Package 2</b>	10
<b>Package 2 Height</b>	7.5 cm
<b>Package 2 Width</b>	19.5 cm
<b>Package 2 Length</b>	21.5 cm
<b>Package 2 Weight</b>	680.0 g

## Contractual warranty

<b>Warranty</b>	18 months
-----------------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations